




FITTINGS


TEE PIECE WITH 1 CONNECTION



DESCRIPTION

Pressfitting Tee piece for multilayer pipe \varnothing 20x2 mm with connection \varnothing 8x1 mm


TEE PIECE WITH 2 CONNECTIONS



DESCRIPTION

Press fitting Tee piece for multi-layer pipe \varnothing 20x2 mm with 2 connections for PE-RT pipe \varnothing 8x1 mm


TEE PIECE WITH 4 CONNECTIONS



DESCRIPTION

Pressfitting Tee piece for multi-layer pipe \varnothing 20x2 mm with 4 connections for PE-RT pipe \varnothing 8x1 mm


PLUG



DESCRIPTION

Press-fitting plug for multi-layer pipe \varnothing 20 mm

COUPLING



DESCRIPTION

Coupling \varnothing 8 mm

INSULATION



DESCRIPTION

Elastomer foam insulation for \varnothing 8 mm pipe insulation

MANIFOLD



DESCRIPTION

Modular pre-assembled technopolymer double chamber manifold with terminal unit and flow indicator, valve, air vent, thermometer and drain cock $\varnothing 1 \text{ "x}3/4$. Flow rate from 1Lt/min to 5Lt/min.

02 to 15 circuits

230 V ACTUATOR



DESCRIPTION

Thermal actuator, On-Off type, suitable for manifolds with return valve, with limit switch, integrated auxiliary contact, normally closed

BYPASS VALVE



DESCRIPTION

Adjustable differential by-pass valve with graduated scale from 0 to 0.5 bar.

MICRO-BUBBLE DEAERATOR 1"



DESCRIPTION

Device for eliminating bubbles and micro-bubbles in the circuit.

ADAPTER



DESCRIPTION

Adapter Eurocone $\varnothing 20 \text{ x}3/4$ for connecting the multilayer pipe to the manifold.